

Ki Mobility Rogue2 Express Script



Customer Details						
Client						
Assessor						
Organisation						
	ACC		DSS		Other	
User Weight						

Ki Mobility Rogue2 Express Script

If you only require specifications that fall under the Standard Express Package, you do not need to fill in the reverse page.

		Seat Width		
		16"	18"	20"
Seat Depth	16"	☐	☐	☐
	17"	☐	☐	☐
	18"	☐	☐	☐
	19"	☐	☐	☐
	20"	☐	☐	☐

Express Codes

☐ KIROGUE21616STD	☐ KIROGUE21818STD
☐ KIROGUE21618STD	☐ KIROGUE22018STD
☐ KIROGUE21816STD	

Add ROGUEEXPPACKAGE to all orders

Use KIROGUEXXXXSTD where available

Express Package: (Select optional specifications and alternatives on reverse)

- Standard Seat Sling
- Omit Transit
- 2in Depth Adjustment
- 85 degree Front Frame Bend
- Sling position 0°
- 1in Tapered Frame
- Height adjustable Medium straight back posts with no Push Handle
- Back Angle set to Standard
- Height adjustable Rigidising Bar
- Tension adjust. back upholstery
- Standard Fork
- Angle Adjustable Flip Under Footplates
- 24in Maxx Spoke Performance Pneumatic Black Wheels
- 5x1.5 Soft Roll Aluminium Castors
- Ergo Lite Handrims omit thumb guard
- Rear Wheel Camber set to 2 degrees
- COG set to 0.5"
- Caster Optimised
- Rear Wheel spacing set to 1.5" to accommodate T-Arms
- Quick Release Axles
- Push to Lock Flush Wheel Locks
- T-Arms with Standard Desk Armpads
- Rear Anti Tipppers
- Iridescent Navy Frame

Please note: Express Package includes some upcharge products.

Choose Your Specifications (No additional codes are required on the below parts)

Backrest Height

☐ 13"	☐ 14"	(For 13" - 14" use .ULROGBUPTA1 if back upholstery required)
☐ 15"	☐ 16"	
☐ Refer to box #1		

Backrest Angle

☐ Std	☐ +2°	☐ +4°	☐ +6°
☐ +8°	☐ +10°	☐ -2°	☐ -4°
☐ -6°	☐ -8°	☐ -10°	

Relaxed Back	☐ 0°	☐ +4°	☐ +9°
--------------	-----------------------------	------------------------------	------------------------------

Front Seat Height

16W:	☐ 17.5"	☐ 18"	☐ 18.5"
18W:	☐ 18.5"	☐ 19"	☐ 19.5"
20W:	☐ 19.5"	☐ 20"	☐ 20.5"
☐ Refer to box #7			

Rear Seat Height

16W:	☐ 15"	☐ 15.5"	☐ 16"	☐ 16.5"
	☐ 17"			
18W:	☐ 15"	☐ 15.5"	☐ 16"	☐ 16.5"
	☐ 17"	☐ 17.5"	☐ 18"	
20W:	☐ 17"	☐ 17.5"	☐ 18"	☐ 18.5"
	☐ 19"	☐ 19.5"	☐ 20"	

Seat to Footrest Length

16W:	☐ 13.5"	☐ 14"	☐ 14.5"	☐ 15"
18W:	☐ 14"	☐ 14.5"	☐ 15"	☐ 15.5"
	☐ 16"			
20W:	☐ 15"	☐ 15.5"	☐ 16"	☐ 16.5"
	☐ 17"	☐ 17.5"		
☐ Refer to box #4				

Optional Specifications																																																																																																																						
Backrest Height 1	Push Rim Options (Standard Wheels) 8																																																																																																																					
Swap to Tall (use .ULROG2BOPTL) Only use .ULROGBUPTA - if upholstery required <table style="width: 100%; text-align: center;"> <tr> <td>☐ 17"</td> <td>☐ 18"</td> <td>☐ 19"</td> <td>☐ 20"</td> </tr> </table>	☐ 17"	☐ 18"	☐ 19"	☐ 20"	<table style="width: 100%;"> <tr> <td style="width: 30px;"></td> <td>Plastic coated push rim (.ULEXPHRMPC)</td> </tr> <tr> <td></td> <td>Standard aluminum push rim (.ULEXPHRMSALI)</td> </tr> </table>		Plastic coated push rim (.ULEXPHRMPC)		Standard aluminum push rim (.ULEXPHRMSALI)																																																																																																													
☐ 17"	☐ 18"	☐ 19"	☐ 20"																																																																																																																			
	Plastic coated push rim (.ULEXPHRMPC)																																																																																																																					
	Standard aluminum push rim (.ULEXPHRMSALI)																																																																																																																					
Backrest Upholstery 2																																																																																																																						
<table style="width: 100%;"> <tr> <td style="width: 30px;"></td> <td>Omit Back Upholstery (add narrative)</td> </tr> </table>		Omit Back Upholstery (add narrative)																																																																																																																				
	Omit Back Upholstery (add narrative)																																																																																																																					
Backrest Options 3																																																																																																																						
<table style="width: 100%;"> <tr><td style="width: 30px;"></td><td>Standard Push Handle Med (.ULROGBCKSTDMED)</td></tr> <tr><td></td><td>Standard Push Handle Med (.ULROG2BCKSTDMED)</td></tr> <tr><td></td><td>Standard Push Handle Tall (.ULROGBCKSTD TALL)</td></tr> <tr><td></td><td>Fold Down Push Handle Med (.ULROGBCKFLDMED)</td></tr> <tr><td></td><td>Fold Down Push Handle Tall (.ULROGBCKFLD TALL)</td></tr> </table>		Standard Push Handle Med (.ULROGBCKSTDMED)		Standard Push Handle Med (.ULROG2BCKSTDMED)		Standard Push Handle Tall (.ULROGBCKSTD TALL)		Fold Down Push Handle Med (.ULROGBCKFLDMED)		Fold Down Push Handle Tall (.ULROGBCKFLD TALL)																																																																																																												
	Standard Push Handle Med (.ULROGBCKSTDMED)																																																																																																																					
	Standard Push Handle Med (.ULROG2BCKSTDMED)																																																																																																																					
	Standard Push Handle Tall (.ULROGBCKSTD TALL)																																																																																																																					
	Fold Down Push Handle Med (.ULROGBCKFLDMED)																																																																																																																					
	Fold Down Push Handle Tall (.ULROGBCKFLD TALL)																																																																																																																					
Footrest Options 4																																																																																																																						
<table style="width: 100%;"> <tr> <td style="width: 30px;">☐</td> <td>High Mount Alum. Ang. Adj. Footplates</td> <td style="width: 100px; text-align: right;">A</td> </tr> <tr> <td></td> <td> <table style="width: 100%; text-align: center;"> <tr> <td></td><td>5"</td><td>6"</td><td>7"</td><td>8"</td><td>9"</td><td>10"</td><td>11"</td><td>12"</td><td>13"</td><td>14"</td> </tr> <tr> <td>16W</td><td></td><td></td><td></td><td></td><td></td><td></td><td></td><td></td><td></td><td></td> </tr> <tr> <td>18W</td><td></td><td></td><td></td><td></td><td></td><td></td><td></td><td></td><td></td><td></td> </tr> <tr> <td>20W</td><td></td><td></td><td></td><td></td><td></td><td></td><td></td><td></td><td></td><td></td> </tr> </table> </td> <td></td> </tr> <tr> <td></td> <td colspan="10">(.ULROGFPLHM)</td> </tr> </table> <table style="width: 100%;"> <tr> <td style="width: 30px;">☐</td> <td>Alum. Ang. Adj. Footplates</td> <td style="width: 100px; text-align: right;">B</td> </tr> <tr> <td></td> <td> <table style="width: 100%; text-align: center;"> <tr> <td></td><td>13.5"</td><td>14"</td><td>14.5"</td><td>15"</td><td>15.5"</td><td>16"</td><td>16.5"</td><td>17"</td><td>17.5"</td> </tr> <tr> <td>16W</td><td></td><td></td><td></td><td></td><td></td><td></td><td></td><td></td><td></td> </tr> <tr> <td>18W</td><td></td><td></td><td></td><td></td><td></td><td></td><td></td><td></td><td></td> </tr> <tr> <td>20W</td><td></td><td></td><td></td><td></td><td></td><td></td><td></td><td></td><td></td> </tr> </table> </td> <td></td> </tr> <tr> <td></td> <td colspan="9">(.ULROGFPLAL or .ULROG2FPLAL1)</td> </tr> </table>	☐	High Mount Alum. Ang. Adj. Footplates	A		<table style="width: 100%; text-align: center;"> <tr> <td></td><td>5"</td><td>6"</td><td>7"</td><td>8"</td><td>9"</td><td>10"</td><td>11"</td><td>12"</td><td>13"</td><td>14"</td> </tr> <tr> <td>16W</td><td></td><td></td><td></td><td></td><td></td><td></td><td></td><td></td><td></td><td></td> </tr> <tr> <td>18W</td><td></td><td></td><td></td><td></td><td></td><td></td><td></td><td></td><td></td><td></td> </tr> <tr> <td>20W</td><td></td><td></td><td></td><td></td><td></td><td></td><td></td><td></td><td></td><td></td> </tr> </table>		5"	6"	7"	8"	9"	10"	11"	12"	13"	14"	16W											18W											20W													(.ULROGFPLHM)										☐	Alum. Ang. Adj. Footplates	B		<table style="width: 100%; text-align: center;"> <tr> <td></td><td>13.5"</td><td>14"</td><td>14.5"</td><td>15"</td><td>15.5"</td><td>16"</td><td>16.5"</td><td>17"</td><td>17.5"</td> </tr> <tr> <td>16W</td><td></td><td></td><td></td><td></td><td></td><td></td><td></td><td></td><td></td> </tr> <tr> <td>18W</td><td></td><td></td><td></td><td></td><td></td><td></td><td></td><td></td><td></td> </tr> <tr> <td>20W</td><td></td><td></td><td></td><td></td><td></td><td></td><td></td><td></td><td></td> </tr> </table>		13.5"	14"	14.5"	15"	15.5"	16"	16.5"	17"	17.5"	16W										18W										20W												(.ULROGFPLAL or .ULROG2FPLAL1)									
☐	High Mount Alum. Ang. Adj. Footplates	A																																																																																																																				
	<table style="width: 100%; text-align: center;"> <tr> <td></td><td>5"</td><td>6"</td><td>7"</td><td>8"</td><td>9"</td><td>10"</td><td>11"</td><td>12"</td><td>13"</td><td>14"</td> </tr> <tr> <td>16W</td><td></td><td></td><td></td><td></td><td></td><td></td><td></td><td></td><td></td><td></td> </tr> <tr> <td>18W</td><td></td><td></td><td></td><td></td><td></td><td></td><td></td><td></td><td></td><td></td> </tr> <tr> <td>20W</td><td></td><td></td><td></td><td></td><td></td><td></td><td></td><td></td><td></td><td></td> </tr> </table>		5"	6"	7"	8"	9"	10"	11"	12"	13"	14"	16W											18W											20W																																																																																			
	5"	6"	7"	8"	9"	10"	11"	12"	13"	14"																																																																																																												
16W																																																																																																																						
18W																																																																																																																						
20W																																																																																																																						
	(.ULROGFPLHM)																																																																																																																					
☐	Alum. Ang. Adj. Footplates	B																																																																																																																				
	<table style="width: 100%; text-align: center;"> <tr> <td></td><td>13.5"</td><td>14"</td><td>14.5"</td><td>15"</td><td>15.5"</td><td>16"</td><td>16.5"</td><td>17"</td><td>17.5"</td> </tr> <tr> <td>16W</td><td></td><td></td><td></td><td></td><td></td><td></td><td></td><td></td><td></td> </tr> <tr> <td>18W</td><td></td><td></td><td></td><td></td><td></td><td></td><td></td><td></td><td></td> </tr> <tr> <td>20W</td><td></td><td></td><td></td><td></td><td></td><td></td><td></td><td></td><td></td> </tr> </table>		13.5"	14"	14.5"	15"	15.5"	16"	16.5"	17"	17.5"	16W										18W										20W																																																																																						
	13.5"	14"	14.5"	15"	15.5"	16"	16.5"	17"	17.5"																																																																																																													
16W																																																																																																																						
18W																																																																																																																						
20W																																																																																																																						
	(.ULROGFPLAL or .ULROG2FPLAL1)																																																																																																																					
Side Guards (not available with T-Arms) 5																																																																																																																						
<table style="width: 100%;"> <tr> <td style="width: 30px;"></td> <td>Clamp On Side Guards (.ULROGSDGDC)</td> </tr> </table>		Clamp On Side Guards (.ULROGSDGDC)																																																																																																																				
	Clamp On Side Guards (.ULROGSDGDC)																																																																																																																					
Camber 6																																																																																																																						
<table style="width: 100%;"> <tr> <td style="width: 30px;"></td> <td style="width: 100px; text-align: center;">0°</td> <td style="width: 100px; text-align: center;">4°</td> <td style="width: 100px;">Rogue2</td> </tr> <tr> <td></td> <td style="text-align: center;">(.ULROG2CAM0)</td> <td style="text-align: center;">(.ULROG2CAM4)</td> <td></td> </tr> </table> <table style="width: 100%;"> <tr> <td style="width: 30px;"></td> <td style="width: 100px; text-align: center;">0°</td> <td style="width: 100px; text-align: center;">4°</td> <td style="width: 100px;">Rogue</td> </tr> <tr> <td></td> <td style="text-align: center;">(.ULROGCAM0)</td> <td style="text-align: center;">(.ULROGCAM4)</td> <td></td> </tr> </table>		0°	4°	Rogue2		(.ULROG2CAM0)	(.ULROG2CAM4)			0°	4°	Rogue		(.ULROGCAM0)	(.ULROGCAM4)																																																																																																							
	0°	4°	Rogue2																																																																																																																			
	(.ULROG2CAM0)	(.ULROG2CAM4)																																																																																																																				
	0°	4°	Rogue																																																																																																																			
	(.ULROGCAM0)	(.ULROGCAM4)																																																																																																																				
Castor Options 7																																																																																																																						
<table style="width: 100%;"> <tr> <td style="width: 30px;"></td> <td>4 x 1.5 Soft Roll Castors (.ULROGCASSR4)</td> </tr> <tr> <td></td> <td>For 16" Width, Front Seat Height 17"</td> </tr> <tr> <td></td> <td>For 18" Width, Front Seat Height 18"</td> </tr> <tr> <td></td> <td>For 20" Width, Front Seat Height 19"</td> </tr> </table>		4 x 1.5 Soft Roll Castors (.ULROGCASSR4)		For 16" Width, Front Seat Height 17"		For 18" Width, Front Seat Height 18"		For 20" Width, Front Seat Height 19"																																																																																																														
	4 x 1.5 Soft Roll Castors (.ULROGCASSR4)																																																																																																																					
	For 16" Width, Front Seat Height 17"																																																																																																																					
	For 18" Width, Front Seat Height 18"																																																																																																																					
	For 20" Width, Front Seat Height 19"																																																																																																																					
Natural Fit: 8																																																																																																																						
<table style="width: 100%;"> <tr> <td style="width: 30px;"></td> <td>Thumb grip regular (.ULEXPHRMTGREG)</td> </tr> </table>		Thumb grip regular (.ULEXPHRMTGREG)																																																																																																																				
	Thumb grip regular (.ULEXPHRMTGREG)																																																																																																																					
Ergonomic Fit: 9																																																																																																																						
<table style="width: 100%;"> <tr> <td style="width: 30px;"></td> <td>Ergo Lite Regular (.ULEXPHRMELREG)</td> </tr> <tr> <td></td> <td>Short Tabs (.ULEXPHRMSTAB)</td> </tr> </table>		Ergo Lite Regular (.ULEXPHRMELREG)		Short Tabs (.ULEXPHRMSTAB)																																																																																																																		
	Ergo Lite Regular (.ULEXPHRMELREG)																																																																																																																					
	Short Tabs (.ULEXPHRMSTAB)																																																																																																																					
Rear Wheel Kit - Low profile tyres 9																																																																																																																						
<table style="width: 100%;"> <tr> <td style="width: 30px;"></td> <td>Rear wheel kit (KIEXPWHL02)</td> </tr> <tr> <td></td> <td>Includes the following:</td> </tr> <tr> <td></td> <td>• Spinergy spox black 24"</td> </tr> <tr> <td></td> <td>• Low profile - Schwalbe Marathon Plus Evolution 1"</td> </tr> <tr> <td></td> <td>• Natural fit LT omit thumb grip</td> </tr> </table>		Rear wheel kit (KIEXPWHL02)		Includes the following:		• Spinergy spox black 24"		• Low profile - Schwalbe Marathon Plus Evolution 1"		• Natural fit LT omit thumb grip																																																																																																												
	Rear wheel kit (KIEXPWHL02)																																																																																																																					
	Includes the following:																																																																																																																					
	• Spinergy spox black 24"																																																																																																																					
	• Low profile - Schwalbe Marathon Plus Evolution 1"																																																																																																																					
	• Natural fit LT omit thumb grip																																																																																																																					
Wheel Locks 10																																																																																																																						
<table style="width: 100%;"> <tr> <td style="width: 30px;"></td> <td>24" Maxx Spoke Low Profile Schwalbe Marathon Plus Ergo Lite Omit thumb grip (.ULEXP24MAXLPFEL)</td> </tr> <tr> <td></td> <td>Plastic coated push rim (.ULEXPHRMPC)</td> </tr> <tr> <td></td> <td>Standard aluminum push rim (.ULEXPHRMSALI)</td> </tr> </table>		24" Maxx Spoke Low Profile Schwalbe Marathon Plus Ergo Lite Omit thumb grip (.ULEXP24MAXLPFEL)		Plastic coated push rim (.ULEXPHRMPC)		Standard aluminum push rim (.ULEXPHRMSALI)																																																																																																																
	24" Maxx Spoke Low Profile Schwalbe Marathon Plus Ergo Lite Omit thumb grip (.ULEXP24MAXLPFEL)																																																																																																																					
	Plastic coated push rim (.ULEXPHRMPC)																																																																																																																					
	Standard aluminum push rim (.ULEXPHRMSALI)																																																																																																																					
Natural Fit: 10																																																																																																																						
<table style="width: 100%;"> <tr> <td style="width: 30px;"></td> <td>Standard gr handrim for MAXX SP (.ULCATHRMNF02)</td> </tr> </table>		Standard gr handrim for MAXX SP (.ULCATHRMNF02)																																																																																																																				
	Standard gr handrim for MAXX SP (.ULCATHRMNF02)																																																																																																																					
Ergonomic Fit: 11																																																																																																																						
<table style="width: 100%;"> <tr> <td style="width: 30px;"></td> <td>Ergo Lite Regular (.ULEXPHRMELREG)</td> </tr> <tr> <td></td> <td>Short Tabs (.ULEXPHRMSTAB)</td> </tr> </table>		Ergo Lite Regular (.ULEXPHRMELREG)		Short Tabs (.ULEXPHRMSTAB)																																																																																																																		
	Ergo Lite Regular (.ULEXPHRMELREG)																																																																																																																					
	Short Tabs (.ULEXPHRMSTAB)																																																																																																																					
Rogue 2 Options 11																																																																																																																						
<table style="width: 100%;"> <tr> <td style="width: 30px;"></td> <td>User Activated Anti Tips (No more than 2" dump .ULROG2UANTTP)</td> </tr> </table>		User Activated Anti Tips (No more than 2" dump .ULROG2UANTTP)																																																																																																																				
	User Activated Anti Tips (No more than 2" dump .ULROG2UANTTP)																																																																																																																					
Accessories 12																																																																																																																						
<table style="width: 100%;"> <tr> <td style="width: 30px;"></td> <td>Clear Spoke Guards (.ULROGSPGCL24)</td> </tr> <tr> <td></td> <td>Impact Guards (.ULROGIMG)</td> </tr> </table>		Clear Spoke Guards (.ULROGSPGCL24)		Impact Guards (.ULROGIMG)																																																																																																																		
	Clear Spoke Guards (.ULROGSPGCL24)																																																																																																																					
	Impact Guards (.ULROGIMG)																																																																																																																					
Bodypoint Belt Options: 12																																																																																																																						
<table style="width: 100%;"> <tr> <td style="width: 30px;"></td> <td>Bodypoint 2pt belt – Centre Pull Flat Mount (BPHB205-M46-A1) + (BPHW200-90-2)</td> </tr> <tr> <td></td> <td>Bodypoint 4pt belt Centre Pull Flat Mount (BPHB405-M46-A1) + (BPHW200-90-2)</td> </tr> <tr> <td></td> <td>Bodypoint Evoflex Pelvic Stabiliser (BPEB205-M46) + (BPHW200-90-2)</td> </tr> <tr> <td></td> <td>Bodypoint Aeromesh Calf Strap (BPSP103M)</td> </tr> </table>		Bodypoint 2pt belt – Centre Pull Flat Mount (BPHB205-M46-A1) + (BPHW200-90-2)		Bodypoint 4pt belt Centre Pull Flat Mount (BPHB405-M46-A1) + (BPHW200-90-2)		Bodypoint Evoflex Pelvic Stabiliser (BPEB205-M46) + (BPHW200-90-2)		Bodypoint Aeromesh Calf Strap (BPSP103M)																																																																																																														
	Bodypoint 2pt belt – Centre Pull Flat Mount (BPHB205-M46-A1) + (BPHW200-90-2)																																																																																																																					
	Bodypoint 4pt belt Centre Pull Flat Mount (BPHB405-M46-A1) + (BPHW200-90-2)																																																																																																																					
	Bodypoint Evoflex Pelvic Stabiliser (BPEB205-M46) + (BPHW200-90-2)																																																																																																																					
	Bodypoint Aeromesh Calf Strap (BPSP103M)																																																																																																																					

